

Filtre	Densité optique	Réduction de la lumière (diaph)	Vitesse obturation							
			1/4000	1/1000	1/250	1/60	1/15	1/4	1sec	4sec
Sans filtre	0	0	1/4000	10/1000	1/250	1/60	1/15	1/4	1 sec	4 sec
ND2	0.3	1	1/2000	1/500	1/125	1/30	1/8	1/2	2 sec	8 sec
Polarisant	0.6	2	1/1000	1/250	1/60	1/15	¼	1 sec	4 sec	16 sec
ND4	0.6	2	1/1000	1/250	1/60	1/15	¼	1 sec	4 sec	16 sec
ND8	0.9	3	1/500	1/125	1/30	1/8	½	2 sec	8 sec	32 sec
ND16	1.2	4	1/250	1/60	1/15	¼	1 sec	4 sec	16 sec	1 min
ND32	1.5	5	1/125	1/30	1/8	½	2 sec	8 sec	32 sec	2 min
ND64	1.8	6	1/60	1/8	1/4	1 sec	4 sec	16 sec	1 min	4 min
ND256	2.4	8	1/15	1/4	1 sec	4 sec	16 sec	1 min	4 min	16 min
ND400	2.6	8 2/3	1/10	0.4 sec	1.6 sec	6 sec	25 sec	1 :40 min	6 :40 min	26 min
ND1000	3	10	1/4	1 sec	4 sec	16 sec	1 min	4 min	16 min	64 min